


DRY-CABI-GB

GLOVE-BOX Features of DRY-CABI-GB



All custom-made specifications: Dehydration system standard equipment, nitrogen specification, HEPA filter specification, high humidity specification, etc.

Custom-made specifications for all items


According to the desired material, shape and size I will produce.

Dewatering device standard equipment

Keep the inside of GB

Nitrogen specification

Nitrogen specifications suitable for operations that dislike oxygen are also possible.




HEPA filter


HEPA filter specifications suitable for use with highly physiologically active drugs are also possible.

Optional Accessories

LED light, internal shelf, dew point meter, hygrometer, oxygen meter. We support various optional products.



<Mechanism of dehydration device>




Dehydrated in the GB with a high-performance dewatering device developed by applying the technology developed in the 「DRY-CABI」, which has 36 years of experience. The semi-automatic control of the desiccant regeneration makes it possible to use it repeatedly for a long period without maintenance.. As no circulation pump is used, compact, low vibration, low operation noise and low power consumption. It can be widely used for the handling of hygroscopic materials and drugs, and for operations that dislike high humidity.

DRY-CABI-GB Three types of dewatering devices

ST Type	E Type	SE Type
Dew point less than -40°C Low dew point in GB with powerful dewatering device	Dew point below -20°C Rapid dewatering is possible despite the low cost specifications	Humidity 10% or less Rh Bargain machine that you can use casually

Change in dew point and humidity according to the type of moisture device



※1 There is a performance difference between the type of dewatering device and the size of the glove box capacity.

※2 Dehydration performance declines as desiccants absorb moisture (Revived by playing back).

※For details, please request a glove box exclusive catalog. Or, please visit the homepage.

<http://www.dry-cabi-gb.com>