



Digital Dual LED Hygrometer Special Series

H-155WD-MII (Capacity 152L)

NOMENCLATURE



◆ **Blue number** indicates the dimensions of storage space.
 ◆ **Green arrow** shows the minimum position between the shelf and the bottom.
 Each shelf board is adjustable, and is removable for your convenience.



Name	Specification
------	---------------

- | | |
|-------------------|--|
| ① Cabinet | : High quality steel plate (0.8mm), hard coated with melamine resin (Black color). |
| ② Door | : 2 doors PVC flame, clear tempered glass with the corner of silk screen printed, magnetic packing. |
| ③ Shelf | : 3 steel boards covered with the Photocatalytic navy blue cushion sheets. |
| ④ Lock-Handle | : 2 Handles with key (2pcs) |
| ⑤ Hygrometer | : Digital Dual LED hygrometer, humidity shown both inside and outside housing |
| ⑥ Caster | : 4 casters, with stopper only front 2 casters |
| ⑦ Tray | : Steel tray is convenient as a pouch 1pc, with plastic tray for battery charging. |
| ⑧ Center Pillar | : When put a long lens, are removable, take off an upper screw of the backside of the pillar and lift a pillar on the top and go down before |
| ⑨ Door packing | : Magnet PVC edge, ensures air tightness |
| ⑩ Pillar for hook | : For setting shelf board (4 pillars) |
| ⑪ Controller | : Humidity controller |
| ⑫ Dehumidifier | : Desiccant system, latest high and technological Memory alloy, IC timer, with a humidity controller for only dehumidifying. |
| ⑬ Top outlet | : User friendly top outlet helps battery charging (Max 500W/H) |
| ⑭ Spare screw | : Double layer connection screw, wall hung tip-resistant hook. |
| ⑮ Bottom plate | : Steel |
| ⑯ Power source | : AC100~120V 50/60Hz 0.3~3.6W/H
AC220~240V 50/60Hz 0.15~1.8W/H
The absorption & ventilation cycle of new drying unit upgraded to 4 hours (3 hours and 30 minutes absorption and 30 minutes ventilation). |
| ⑰ Nameplate | : YES |
| Weight | : 25Kg |



*Note: Specification are subject to change without notice



Since 1983

TOLIHAN CORP.

An inquiry, the communication by E-mail.

E-mail info@dry-cabi.co.jp

21-6, Higashi-Ueno, 3-chome, Taiko-ku, Tokyo Japan 110-0015

Phone:81-3-3833-0614 Fax:81-3-3833-0616

URL <http://www.dry-cabi.co.jp/english.html>